



THE NEW ICX-DIM ANALOGS

For standard ICX implants ● Ø3.45 ● Ø3.75 ● Ø4.1 ● Ø4.8
and for ● Ø 3.3 ICX-Implants

Two-piece repositionable implant analog
Precisely positionable
Reusable



[Click here for medentis
downloads CAD libraries](#)



The conventional CAD CAM BL analogs C-006-010003 can also be used in the new slot geometry of the new database (EXOCAD and 3Shape).

The new ICX-DIM analogs for printed models are available for both the standard 3.45-4.8 line as well as the 3.3 line.

ICX-DENTAS
exocad
3shape 